


PREMIUM RESIN DIAMONDS FOR EXCEPTIONAL POLISHING

Move seamlessly from low grit metal bond diamonds, to **Hybrid Resin** diamonds for honing, and then super fine **Standard Resin** to achieve a high-gloss polish.



HYBRID

HYBRID Resin Diamond Tooling transitions perfectly after grinding with metal bond diamonds, and before polishing with standard resin. Wet hybrids can even be used for the initial cut, eliminating the need for metal bond tooling!




- 50
GRIT
GREY
- 100
GRIT
BLACK
- 200
GRIT
BLUE
- 400
GRIT
RED

GRIT	DRY	WET
50	50HRD	50HRW
100	100HRD	100HRW
200	200HRD	200HRW
400	400HRD	400HRW

STANDARD

Advance to STANDARD Resin Diamond Tooling in the higher grits (400–3000) for polishing to a stunning high-gloss.



- 400
GRIT
RED
- 800
GRIT
WHITE
- 1500
GRIT
YELLOW
- 3000
GRIT
GREEN

GRIT	DRY
400	400SR
800	800SR
1500	1500SR
3000	3000SR